

# CEEVAC PORTABLE SUCTION PUMP

## MAINS / BATTERY OPERATED

Ceevac continues the tradition of the Clements CarriVac, providing the same dependable level of performance in a lighter, more compact form factor.

Ceevac offers the convenience of a lightweight, fully portable suction source with the versatility of three different power sources - mains power, vehicle 12 volt DC and an internal rechargeable battery.

Designed for high vacuum performance, reliability and minimal maintenance, Ceevac is ideal for emergency services, home use or as an alternative to wall suction.

- Maximum Vacuum: -80 kPa [ -600 mmHg]
- Maximum Flow : 25 litres/minute
- 60 minute battery run time
- Direct vacuum regulation
- Compact and lightweight



# CLEMENTS

 **Evocare**  
[www.evocare.com.au](http://www.evocare.com.au)  
Ph: 07 3355 8000 Fax: 07 3355 5043  
Email: [sales@evocare.com.au](mailto:sales@evocare.com.au)

# CEEVAC PORTABLE SUCTION PUMP

TECHNICAL SPECIFICATION	
Power Rating	100 - 240V 50/60Hz 100 VA
Maximum Vacuum	-80 kPa, [-600 mmHg]
Maximum Flow Rate	25 L/min (measured through 1L reusable jar)
Gauge	Bourdon tube type, dual scale, graduated in kPa and mmHg
Gauge Range	0 to -100 kPa graduated at 5 kPa 0 to -760 mmHg graduated at 20 mmHg
Vacuum Regulator	Needle valve type
Pump type	Diaphragm - motor and pump combined
Collection Canister	1 Litre autoclavable, shatterproof polycarbonate jar Optional: 1 Litre disposable liner jar, 2 Litre disposable liner jar
Overflow Protection	Float valve mechanism / Hydrophobic filter
Internal Battery	Fully sealed, replaceable SLA
Battery Run Time	60 minutes
Battery Indicator	Charging / Low Battery LED / Low Battery Beeper
Battery Charger	External
Charging Time	4 hours
Dimensions	H 210 mm, W 180 mm, L 350 mm
Weight	4.4 kg
GMDN	36777
Device Class	Class IIA
Operation Mode	Continuous operation

PART NUMBERS	
SUC 81030	High Vacuum High Flow Portable Suction Pump with 1 x 1L Reusable Collection Jar
SUC 81030 001	Kit, 1L Reusable Collection Jar (Pack 1) (1L Reusable Jar, Lid)
SUC 81030 KIT2	Disposable Liner KIT for 2L liner VAL-201
VAL-201	2L Vacsax disposable liner (box of 30)
3833-007/S	Tapered Connector for Vacsax liners (Tubing connection)

All specifications are subject to change without notice. Please check the exact specification when ordering.

BMDi TUTA Healthcare Limited  
Unit 4B, 128-130 Frances St, NSW 2141, Australia  
Telephone +61 2 9466 5300  
Email [info@medaust.com](mailto:info@medaust.com)  
Web [www.medaust.com](http://www.medaust.com)

Rev 5. © Copyright 2015 Medical Australia Limited.

 **Evocare**<sup>®</sup>  
[www.evocare.com.au](http://www.evocare.com.au)  
Ph: 07 3355 8000 Fax: 07 3355 5043  
Email: [sales@evocare.com.au](mailto:sales@evocare.com.au)

**CLEMENTS**