

ACTIVE

BASIC

CUSTOM

Slings		Kids 4 - 6	Kids 6 - 10	Kids 10 - 14	XS	S	M	L	XL	XXL	3XL
Active Micro	polyester				284031	284041	284051	284061	284071	284081	
Active Micro Plus	polyester	281001	281011	281021	281531	281541	281551	281561	281571	281581	
Active Trainer	polyester		283011	283021	283031	283041	283051	283061	283071	283081	
Basic Basic	polyester	270001	270011	270021	270031	270041	270051	270061	270071	270081	270091*
Basic Basic	net	270102	270112	270122	270133	270143	270153	270163	270173	270183	
Basic Low	polyester				271031	271041	271051	271061	271071	271081	
Basic Low	net				271133	271143	271153	271163	271173	271183	
Basic High	polyester	272001	272011	272021	272031	272041	272051	272061	272071	272081	272091**
Basic High	net	272102	272112	272122	272133	272143	272153	272163	272173	272183	
Basic Shell	net				275032	275042	275052	275062	275072		
Basic Hammock	polyester				274031	274041	274051	274061	274071		
Sit-On	net	295001	295011		295031	295041	295051	295061	295071		
Sit-On High	net	296001	296011		296031	296041	296051	296061	296071		
Sit-On Comfort	spacer	293001	293011		293031	293041	293051	293061	293071		
Sit-On Comfort High	spacer	294001	294011		294031	294041	294051	294061	294071		
Custom Amputee	polyester				290031	290041	290051	290061	290071		
Active Vest Kids**	polyester		283111	283121***							
Vest for Standing Shell**	polyester		283511	283521***	283531						


Max lifting capacity for all Guldman ABC slings: 255 kg

- x) Basic Basic and Basic High XXXL can lift up to 500 kg
- xx) Max lifting capacity for Active Vest Kids / Vest for standing Shell: 100 kg
- xxx) Active Vest Kids / Vest for standing Shell: Kids 10-16

Guidelines on choosing the size of a sling

	Kids 4 - 6	Kids 6 - 10	Kids 10 - 14	XS	S	M	L	XL	XXL	3XL
H	45 - 60	55 - 70	68 - 80	75 - 82	80 - 87	85 - 92	90 - 97	95 - 102	95 - 102	95 - 102
W	25 - 30	28 - 35	33 - 38	33 - 37	36 - 40	39 - 43	42 - 45	45 - 49	48 - 52	54 - 58

All dimensions in cm



Normal washing at the indicated temperature



Do not use bleaching agent



Tumble-drying at low temperature



Do not iron



The coloured loops ensure symmetry in the lift and at the same time ease the communication in connection with the lift